

### **Laserglow Product Datasheet**

# LRD-0405 Collimated Diode Laser System

## Laserglow Part Number: D405005FX

This model is listed as **inactive** in our product database. Stock may be limited, and availability is subject to change without notice.

#### **Similar Products:**

For information about the other lasers in this product family visit:

http://www.laserglow.com/D40

#### Ordering:

Order Online Now or Request Quote:

http://www.laserglow.com/D405005FX

#### **Series Specifications:**

Nominal Wavelength	405 nm
Output Type	CW
Laser Source Type	Diode



#### Overview:

The LRD-0405 Series of Collimated Diode (Semiconductor) Lasers are ideal for applications requiring a short wavelength of 405 nm and output power levels from 5 mW to 500 mW with a high level of long-term output power stability.

These lasers are commonly used for various scientific applications involving fluorescence excitation, as well as PIV, spectral analysis, and a broad spectrum of other applications. The driver is available as a complete FDA-compliant system or as an O.E.M. component with significantly reduced dimensions.

Available with both on-board and remote on/off control as well as a wide array of output power and stability levels, Laserglow products are currently being used by some of the world's top universities and other prominent research facilities.

#### **Key Features:**

- Air cooled no need for water cooling or external chiller
- Lightweight, compact design
- Efficient Diode Laser technology runs on standard AC power (85 264 V, 47 63 Hz)
- >10,000 hours continuous maintenance-free operating life
- FDA CDRH Compliant Class IIIb / Class IV enclosure
- 48-hour replacement coverage available for an additional fee on specific models

#### Specifications:

This spec sheet has been generated specifically for part number D405005FX, per your request, and data for the entire series is also displayed for your reference. The specs which are specific to D405005FX have been highlighted below in **red + bold**.

Output Power (mW)	>10, >30, >50	>30, >50	>30, >50, >100, >200, >300, >400, <b>&gt;500</b> , >800, >1000
Output Power Stability (%RMS/4h)	<1, <3	<1, <3	<1, <3, <b>&lt;5</b> , <10
Central Wavelength (nm)	405	406.4	406.4
Wavelength Tolerance (+/- nm)	5	5	5
Divergence (mrad, full angle)	<1	<0.5	<0.5, <2.5x1
Beam Dimensions (mm, 1/e²)	1	2.5	3x2.7, 4
Transverse Mode			<499 mW Near TEM00   >499 mW Multimode
Warm-up Time (minutes)	5	15	5
Spectral Linewidth (nm)		<0.06	<1.2
M²	<1.2		
Polarization Ratio		>50	>50
Beam Pointing Stability (mrad)	<0.05		<0.05
Operating Temperature Range (°C)	10 to 35	20 to 30	10 to 35
Max. Analog Modulation Freq. (Hz)	30000	30000	30000
Max. TTL Modulation Freq. (Hz)	30000	30000	10000, 30000
Modulation Input Signal	0-5 VDC	0-5 VDC	0-5 VDC
Total Power Consumption (W)	9		6, 9, 10, 15
Max. Power Input Duty Cycle	100%	100%	100%
Standard Warranty (months)	12	12	12
MTTF (operational hours)	10000	10000	10000
Weight of Product or Laser Head (kg)	0.6	0.8	0.6
Beam Height from Base Plate (mm)	24.8	30	24.8
Dimensions of Product or Laser Head (mm)	140.7 (l) x 73 (w) x 46.2 (h)	122.5 (l) x 65 (w) x 50 (h)	140.7 (l) x 73 (w) x 46.2 (h)

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the laser is run at a different power level.


Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

#### **Power Supply Options:**

These lasers are available with several different power supply options. The model that you have selected is highlighted below, and any other options are shown for easy reference.

	Power Supply Type:	FR	FE
FDA-Compliant LabSpec	Input Power	85v to 264v	85v to 264v
9 may 2-	Power Supply Weight (kg)	1.5	6.2
The same of the sa	Dimensions (mm)	154 (I) x 155 (w) x 95 (h)	320 (l) x 300 (w) x 123 (h)

	Power Supply Type:	SR
FDA-Compliant Standard	Input Power	85v to 264v
	Power Supply Weight (kg)	1.2
	Dimensions (mm)	133 (l) x 130 (w) x 65 (h)



<sup>\*</sup>Power supply may not be exactly as shown, see dimensional drawings on next 2 pages.

#### **Regulatory Classification:**

The model you have selected (D405005FX) requires the following safety label(s):



<sup>\*</sup>Dimensions for fiber-integrated (I\_) include laser head packaged inside.

#### **Dimensional Drawing - Laser Form Factor: R:**



#### **Dimensional Drawing - Power Supply Form Factor: FR:**



#### **Accessories:**

The most popular accessories for model D405005FX are shown below. For additional details regarding these or other accessories please see our website or contact us directly.

Part Number	Description	
AGF5327XX	LSG-532-NF-7 Fit-Over Safety Goggles 532nm Output: OD 7+ at 190-532 nm CE Certified Full Details: www.laserglow.com/AGF	
ACFVISHXA	FC/PC Fiber Coupler/Collimator for visible spectrum wavelengths (400 to 700 nm) (installed and aligned) 11mm diameter input lens Full Details: <a href="https://www.laserglow.com/ACF">www.laserglow.com/ACF</a>	
ACSVISHXA	SMA-905 Fiber Coupler/Collimator for visible spectrum wavelengths (400 to 700 nm) (installed and aligned) 11mm diameter input lens Full Details: <a href="https://www.laserglow.com/ACS">www.laserglow.com/ACS</a>	
ACALBMXXX	Carrying Case-102 Holds Lab/OEM M, R and S size, standard or LabSpec laser Full Details: <a href="https://www.laserglow.com/ACA">www.laserglow.com/ACA</a>	Included With Laser
AFS2002XX	Armored Fiber With SMA 905 Connectors 200um Core Multimode 2 m length Full Details: <a href="https://www.laserglow.com/AFS">www.laserglow.com/AFS</a>	
AFF2002XX	Armored Fiber With FC/PC Connectors 200um Core Multimode 2m length Full Details: <a href="https://www.laserglow.com/AFF">www.laserglow.com/AFF</a>	

#### FOR MORE INFORMATION PLEASE CONTACT:

LASERGLOW TECHNOLOGIES
99 Ingram Dr. Unit B, North York, ON, Canada M6M2L7
Tel. (416) 729-7976 Fax (716) 322-3510
sales@laserglow.com www.laserglow.com

E&OE: Data included in this sheet may be subject to change without notice.

Please confirm critical specifications with our staff prior to ordering.