

## **Laserglow Product Datasheet**

## LLD-0830 Low-Noise Collimated Diode Laser System

# Laserglow Part Number: J831001FX

#### Similar Products:

For information about the other lasers in this product family visit:

http://www.laserglow.com/J83

#### Ordering:

Order Online Now or Request Quote:

http://www.laserglow.com/J831001FX

#### **Series Specifications:**

<u> </u>	
Nominal Wavelength	830 nm
Output Type	CW
Laser Source Type	Diode



#### Overview:

The LLD-0830 Series of Low-Noise Collimated Diode Lasers are ideal for applications requiring less than 1% noise and output power levels from 10 mW to 2000 mW. These 830 nm NIR lasers maintain a high level of long-term output power stability and long operating lifetime at an aggressively competitive cost.

These lasers are commonly used for fluorescence excitation, PIV, Raman Spectroscopy, and a broad spectrum of other applications. The driver is available as a complete FDA-compliant system or as an O.E.M. component with significantly reduced dimensions.

Laserglow products are currently being used by some of the World's top universities and other prominent research facilities.

#### **Key Features:**

- 1% optical noise (20 Hz-20 MHz)
- · Air cooled no need for water cooling or external chiller
- · Lightweight, compact design
- Efficient DPSS technology runs on standard AC power (85 264 V, 47 63 Hz)
- >10,000 hours continuous maintenance-free operating life
- FDA CDRH Compliant Class IIIb / Class IV enclosure
- 48-hour replacement coverage available for an additional fee on specific models

#### Package Includes:

- Laser Head
- Driver/Power Supply
- Power Cable
- BNC Connector (LabSpec models only)

- Keys, Safety InterlockHard-shell Carrying Case

#### Specifications:

This spec sheet has been generated specifically for part number J831001FX, per your request, and data for the entire series is also displayed for your reference. The specs which are specific to J831001FX have been highlighted below in red + bold.

Output Power (mW)	>10, >50, >100	<b>&gt;100</b> , >200, >300, >500, >1000, >2000
Output Power Stability (%RMS/4h)	<1, <3, <5	<1, <3
Central Wavelength (nm)	830	830
Wavelength Tolerance (+/- nm)	10	5
Divergence (mrad, full angle)	<1	<2.5
Beam Dimensions (mm, 1/e²)	3	5x8
Warm-up Time (minutes)	5	5
Optical Noise Amplitude (%RMS @ 20 Hz - 20 MHz)	<1	<1
Polarization Ratio		>50
Operating Temperature Range (°C)	10 to 35	10 to 35
Max. Analog Modulation Freq. (Hz)	30000	30000
Max. TTL Modulation Freq. (Hz)	30000	30000
Modulation Input Signal	0-5 VDC	0-5 VDC
Max. Power Input Duty Cycle	100%	100%
Standard Warranty (months)	12	12
MTTF (operational hours)	10000	10000
Weight of Product or Laser Head (kg)	0.6	0.6
Beam Height from Base Plate (mm)	24.8	24.8
Dimensions of Product or Laser Head (mm)	140.7 (l) x 73 (w) x 46.2 (h)	140.7 (l) x 73 (w) x 46.2 (h)

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the laser is run at a different power level.

Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

#### **Power Supply Options:**

These lasers are available with several different power supply options. The model that you have selected is highlighted below, and any other options are shown for easy reference.

	Power Supply Type:	FR
FDA-Compliant LabSpec	Input Power	85v to 264v
? Many Arrival	Power Supply Weight (kg)	1.5
	Dimensions (mm)	154 (I) x 155 (w) x 95 (h)

<sup>\*</sup>Power supply may not be exactly as shown, see dimensional drawings on next 2 pages.

### **Regulatory Classification:**

The model you have selected (J831001FX) requires the following safety label(s):



<sup>\*</sup>Dimensions for fiber-integrated (I\_) include laser head packaged inside.

## **Dimensional Drawing - Laser Form Factor: R:**



## **Dimensional Drawing - Power Supply Form Factor: FR:**



#### **Accessories:**

The most popular accessories for model J831001FX are shown below. For additional details regarding these or other accessories please see our website or contact us directly.

Part Number	Description	
-------------	-------------	--

#### FOR MORE INFORMATION PLEASE CONTACT:

LASERGLOW TECHNOLOGIES
99 Ingram Dr. Unit B, North York, ON, Canada M6M2L7
Tel. (416) 729-7976 Fax (716) 322-3510
sales@laserglow.com www.laserglow.com

E&OE: Data included in this sheet may be subject to change without notice.

Please confirm critical specifications with our staff prior to ordering.