

# **Laserglow Product Datasheet**

# LLS-0532 Low-Noise DPSS Laser System

# Laserglow Part Number: L5310B5FX

This model is listed as **inactive** in our product database. Stock may be limited, and availability is subject to change without notice.

#### **Similar Products:**

For information about the other lasers in this product family visit:

http://www.laserglow.com/L53

#### Ordering:

Order Online Now or Request Quote:

http://www.laserglow.com/L5310B5FX

#### **Series Specifications:**

| Nominal Wavelength | 532 nm |
|--------------------|--------|
| Output Type        | CW     |
| Laser Source Type  | DPSS   |



#### Overview:

The LLS-0532 Series of Low-Noise Diode-Pumped Solid-State (DPSS) Lasers are ideal for applications requiring less than 1% noise and output power levels from 5 mW to 20 W. These 532 nm lasers maintain a high level of long-term output power stability and long operating lifetime at an aggressively competitive cost.

These lasers are commonly used for fluorescence excitation, PIV, Raman Spectroscopy, and a broad spectrum of other applications. The driver is available as a complete FDA-compliant system or as an O.E.M. component with significantly reduced dimensions.

Laserglow products are currently being used by some of the World's top universities and other prominent research facilities.

#### **Key Features:**

- 1% optical noise (20 Hz-20 MHz)
- Air cooled no need for water cooling or external chiller
- Lightweight, compact design
- Efficient DPSS technology runs on standard AC power (85 264 V, 47 63 Hz)
- >10,000 hours continuous maintenance-free operating life
- FDA CDRH Compliant Class IIIb / Class IV enclosure
- 48-hour replacement coverage available for an additional fee on specific models

#### Package Includes:

- Laser HeadDriver/Power SupplyPower CableKeys, Safety InterlockHard-shell Carrying Case

#### Specifications:

This spec sheet has been generated specifically for part number L5310B5FX, per your request, and data for the entire series is also displayed for your reference. The specs which are specific to L5310B5FX have been highlighted below in **red + bold**.

| Output Power (mW)                                     | <5, >10, >30, >50, >100, >200, >300 | >100                           | >500, <b>&gt;1000</b> , >1500 | >2000                          | >3000, >4000,<br>>5000       | >8000, >10000, >12000,<br>>15000, >18000, >20000 |
|---|-------------------------------------|--------------------------------|-------------------------------|--------------------------------|------------------------------|--|
| Output Power<br>Stability (%RMS/4h)                   | <1, <2, <3                          | <1, <3                         | <1, <2, <3, <b>&lt;5</b>      | <1, <3, <5                     | <1, <2, <3, <5               | <1, <2, <3, <5                                   |
| Central Wavelength (nm)                               | 531.65                              |                                | 531.65                        | 531.65                         | 531.65                       | 531.65   |
| Wavelength<br>Tolerance (+/- nm)                      | 1                                   |                                | 1                             | 1                              | 1                            | 1  |
| Divergence (mrad, full angle)                         | <1.5                                | <1.5                           | <1.5                          | <2                             | <1.5                         | <2   |
| Beam Dimensions<br>(mm, 1/e²)                         | 1.2                                 | 0.7                            | 2                             | 3                              | 3                            | 4  |
| Warm-up Time<br>(minutes)                             | 10                                  |                                | 10                            | 10                             | 10                           | 10   |
| Optical Noise<br>Amplitude (%RMS<br>@ 20 Hz - 20 MHz) | <1                                  |                                | <1                            | <1                             | <1                           | <1   |
| Spectral Linewidth (nm)                               | <0.2                                |                                | <0.2                          | <0.2                           | <0.1                         | <0.2   |
| M²  | <1.2                                | <1.2                           | <1.2                          | <2                             | <3                           | <3   |
| Polarization Ratio                                    | >100                                |                                | >100                          | >100                           | >100                         | >50  |
| Beam Pointing<br>Stability (mrad)                     | <0.05                               |                                | <0.05                         | <0.05                          | <0.05                        | <0.05  |
| Operating<br>Temperature Range<br>(°C)                | 10 to 35                            |                                | 10 to 35                      | 10 to 35                       | 10 to 35                     | 10 to 35   |
| Total Power<br>Consumption (W)                        | 22, 32                              | 22                             | 70, <b>120</b>                | 125                            |                              |  |
| Max. Power Input<br>Duty Cycle                        | 100%                                | 100%                           | 100%                          | 100%                           | 100%                         | 100%   |
| Standard Warranty (months)                            | 12                                  | 12                             | 12                            | 12                             | 12                           | 12   |
| MTTF (operational hours)                              | 10000                               | 10000                          | 10000                         | 10000                          | 10000                        | 10000  |
| Weight of Product or<br>Laser Head (kg)               | 0.6                                 | 10.2                           | 2                             | 1.6                            | 2.6                          | 6.1  |
| Beam Height from<br>Base Plate (mm)                   | 24.8                                | 113                            | 27.4                          | 45                             | 68.2                         | 93.5   |
| Dimensions of<br>Product or Laser<br>Head (mm)        | 140.8 (l) x 73 (w) x<br>46.2 (h)    | 420 (l) x 142 (w)<br>x 144 (h) | 197 (l) x 70 (w)<br>x 50 (h)  | 211.5 (l) x 88 (w)<br>x 74 (h) | 240 (l) x 99 (w)<br>x 94 (h) | 346 (l) x 140 (w) x 125 (h)                      |

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the laser is run at a different power level.

Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

#### **Power Supply Options:**

These lasers are available with several different power supply options. The model that you have selected is highlighted below, and any other options are shown for easy reference.

|                        | Power Supply Type:          | SM                            | so                             | sw                             | SF                             |
|------------------------|-----------------------------|-------------------------------|--------------------------------|--------------------------------|--------------------------------|
| FDA-Compliant Standard | Input Power                 | 85v to 264v                   | 85v to 264v                    | 85v to 264v                    | 85v to 264v                    |
|                        | Power Supply<br>Weight (kg) | 1.2                           | 2.3                            | 5.1                            | 2.3                            |
|                        | Dimensions (mm)             | 133 (l) x 130 (w) x<br>65 (h) | 238 (I) x 146 (w) x<br>102 (h) | 307 (l) x 168 (w) x<br>123 (h) | 238 (l) x 146 (w) x<br>102 (h) |

|                       | Power Supply Type:          | FW                             | FN                             |
|-----------------------|-----------------------------|--------------------------------|--------------------------------|
| FDA-Compliant LabSpec | Input Power                 | 85v to 264v                    | 85v to 264v                    |
|                       | Power Supply<br>Weight (kg) | 5.2                            | 2.6                            |
| and the same          | Dimensions (mm)             | 307 (l) x 168 (w) x<br>123 (h) | 268 (I) x 145 (w) x<br>106 (h) |

<sup>\*</sup>Power supply may not be exactly as shown, see dimensional drawings on next 2 pages.

### **Regulatory Classification:**

The model you have selected (L5310B5FX) requires the following safety label(s):



<sup>\*</sup>Dimensions for fiber-integrated (I\_) include laser head packaged inside.

# **Dimensional Drawing - Laser Form Factor: 0:**



# **Dimensional Drawing - Power Supply Form Factor: SO:**



#### **Accessories:**

The most popular accessories for model L5310B5FX are shown below. For additional details regarding these or other accessories please see our website or contact us directly.

| Part Number | Description  |                     |
|-------------|--|---------------------|
| AGF5327XX   | LSG-532-NF-7 Fit-Over Safety Goggles 532nm Output: OD 7+ at 190-532 nm CE Certified Full Details: www.laserglow.com/AGF  |                     |
| ACFVISHXA   | FC/PC Fiber Coupler/Collimator for visible spectrum wavelengths (400 to 700 nm) (installed and aligned) 11mm diameter input lens Full Details: <a href="https://www.laserglow.com/ACF">www.laserglow.com/ACF</a>     |                     |
| ACSVISHXA   | SMA-905 Fiber Coupler/Collimator for visible spectrum wavelengths (400 to 700 nm) (installed and aligned) 11mm diameter input lens Full Details: <a href="https://www.laserglow.com/ACS">www.laserglow.com/ACS</a>   |                     |
| AFS2002XX   | Armored Fiber With SMA 905 Connectors 200um Core Multimode 2 m length Full Details: <a href="https://www.laserglow.com/AFS">www.laserglow.com/AFS</a>  |                     |
| AFF2002XX   | Armored Fiber With FC/PC Connectors 200um Core Multimode 2m length Full Details: <a href="https://www.laserglow.com/AFF">www.laserglow.com/AFF</a>   |                     |
| TBK         | Complete optics kits with breadboard mounting hardware.  External modulators, variable attenuators, free-space fiber launch systems  Full Details: <a href="https://www.laserglow.com/TBK">www.laserglow.com/TBK</a> |                     |
| ACALBHFXX   | Carrying Case-103 Holds Lab/OEM H, F and O size Standard/LabSpec laser Full Details: <a href="https://www.laserglow.com/ACA">www.laserglow.com/ACA</a>   | Included With Laser |

### FOR MORE INFORMATION PLEASE CONTACT:

LASERGLOW TECHNOLOGIES
99 Ingram Dr. Unit B, North York, ON, Canada M6M2L7
Tel. (416) 729-7976 Fax (716) 322-3510
sales@laserglow.com www.laserglow.com

E&OE: Data included in this sheet may be subject to change without notice.

Please confirm critical specifications with our staff prior to ordering.