

# **Laserglow Product Datasheet**

# LQS-0660 Passively Q-Switched Laser System

# Laserglow Part Number: Q660021SX

#### **Similar Products:**

For information about the other lasers in this product family visit:

http://www.laserglow.com/Q66

#### Ordering:

Order Online Now or Request Quote:

http://www.laserglow.com/Q660021SX

# **Series Specifications:**

<u> </u>	
Nominal Wavelength	660 nm
Output Type	Q-Switched
Laser Source Type	DPSS



#### Overview:

The LQS-0660 Series of Diode-Pumped Solid-State (DPSS) Q-Switched Lasers are ideal for applications requiring a very high peak power or short pulse duration at 660 nm.

These lasers are commonly used for high-speed imaging, Raman spectroscopy, material processing, and a broad range of other applications. The driver is available as a plug-and-play benchtop system or an O.E.M. component designed for system integration.

#### **Key Features:**

- Pulse energy of 1 uJ 2 uJ
- Pulse repetition rate of 1 Hz 2 kHz
- Pulse duration of 15 ns
- · Air cooled
- Runs on standard AC power (85 264 V, 47 63 Hz)
- 10,000 hour maintenance-free operating life (Expected)
- FDA/CDRH compliant Class IV enclosure

#### Package Includes:

- · Laser Head
- Driver/Power Supply
- Power Cable
- BNC Connector (LabSpec models only)
- Keys, Safety Interlock
- Hard-shell Carrying Case

#### Specifications:

This spec sheet has been generated specifically for part number Q660021SX, per your request, and data for the entire series is also displayed for your reference. The specs which are specific to Q660021SX have been highlighted below in **red + bold**.

a a	
Output Power (mW)	>2, <b>&gt;4</b> , >10
Single Pulse Energy (µJ)	1, <mark>2</mark> , 10
Optimal Pulse Frequency (Hz)	2000
Output Power Stability (%RMS/4h)	<b>&lt;1</b> , <b>&lt;3</b> , <b>&lt;5</b>
Central Wavelength (nm)	660
Wavelength Tolerance (+/- nm)	1
Divergence (mrad, full angle)	<1.5
Beam Dimensions (mm, 1/e²)	1.2
Warm-up Time (minutes)	10
Avg. Pulse Duration (ns)	15
Approximate Peak Power (W)	100, 330
M²	<1.2
Operating Temperature Range (°C)	10 to 35
Max. TTL Modulation Freq. (Hz)	20000
Minimum Pulsing Frequency (Hz)	1
Modulation Input Signal	0-5 VDC
Max. Power Input Duty Cycle	100%
Standard Warranty (months)	12
MTTF (operational hours)	10000
Weight of Product or Laser Head (kg)	0.6
Beam Height from Base Plate (mm)	24.8
Dimensions of Product or Laser Head (mm)	140.8 (l) x 73 (w) x 46.2 (h)

CW: All specifications are based on performance at full output power and after the specified warmup period. Output characteristics may change if the laser is run at a different power level.

Q-Switched: Specifications are based on the laser pulsing at the specified design frequency. Output characteristics may change if the laser is run at a different frequency.

#### **Power Supply Options:**

These lasers are available with several different power supply options. The model that you have selected is highlighted below, and any other options are shown for easy reference.

	Power Supply Type:	SM
FDA-Compliant Standard	Input Power	85v to 264v
	Power Supply Weight (kg)	1.2
	Dimensions (mm)	133 (l) x 130 (w) x 65 (h)

<sup>\*</sup>Power supply may not be exactly as shown, see dimensional drawings on next 2 pages.

# **Regulatory Classification:**

The model you have selected (Q660021SX) requires the following safety label(s):



<sup>\*</sup>Dimensions for fiber-integrated (I\_) include laser head packaged inside.

# **Dimensional Drawing - Laser Form Factor: M:**



## **Dimensional Drawing - Power Supply Form Factor: SM:**



#### **Accessories:**

The most popular accessories for model Q660021SX are shown below. For additional details regarding these or other accessories please see our website or contact us directly.

Part Number	Description	
-------------	-------------	--

#### FOR MORE INFORMATION PLEASE CONTACT:

LASERGLOW TECHNOLOGIES
99 Ingram Dr. Unit B, North York, ON, Canada M6M2L7
Tel. (416) 729-7976 Fax (716) 322-3510
sales@laserglow.com www.laserglow.com

E&OE: Data included in this sheet may be subject to change without notice.

Please confirm critical specifications with our staff prior to ordering.